


TOLERANCE: ±0.05, THICKNESS: 1.6mm
RECOMMENDED PCB LAYOUT
(TOP VIEW)

Ordering Information

YTC-2PH25 - XX XX S001 X X X

No.Of Pins Per Row 01~40	Standard Plating 01=Gold Flash 02=Gold 3U 11=Plating Tin XX=Select Plating	Pin Length 001=6.0/3.0 002=5.84/2.8 XXX=Select A/B	Insulation Material P=PBT T=NL6T L=LCP	Contact Material B=Brass P=Phone Bronze	Packing Material A=PE Bag B=Box D=Tube
--------------------------------	---	---	--	---	--

Dimension Antitheses List		
Item	A	B
Standard	6.0	3.0
Select		



Specifications

Current Rating: 3Amp
Insulation Resistance: 1000MΩ Min.
Dielectric Withstanding: 600V AC
Contact Resistance: 20mΩ Max.
Operating Temperature: -40°C to +105°C

Materials

Contact Material: Brass
Insulation Material: Polyester, UL 94V-0
6T

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD	页码 (SHEET)	1/1	单位(UNIT): MM
	版本 (REV)	A1	比例(SCALE)
	日期 (DATE)	2021.10.12	
	设计 (DESIGN)	LUO	GENERAL TOLERANCE
	品名 (ITEM NO)	2.54MM PIN HEADER DUAL ROWS DIP TYPE BASE 2.54H	
料号 (PART NO)	YTC-2PH25-XXXX-SXX1-XXX	审核 (CHECKED)	ROGER LI
图号 (DWG NO)	PH2.54	核准 (APPROVED)	ROC ZHAO

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com