


ACCLIMATE



IP68 SEALED USB CABLE PLUG

SPECIFICATIONS

For complete specifications see www.samtec.com?RCU

Insulator Material:
Glass Filled Thermoplastic
Contact Material:
Phosphor Bronze
Current Rating:
4.2 A per pin
(1 pin powered)
Operating Temp Range:
-20 °C to +80 °C
Shield Material:
Phosphor Bronze
Wire:
20 AWG (Power)
25 AWG (Signal)
28 AWG (Drain)

DUST CAPS

-AMS = DCA-RCU-01-01-A -BMS = DCA-RCU-01-01-B

ALSO AVAILABLE (MOQ Required)

- Other wire lengths
- End option 2 with -AMS, -BMS or -BM

Mates with: RPCU, RPBU

