VW3A8306TF10

Modbus "T" tap-off - 1 x RJ45 male and 2 x RJ45 female - cable 1 m



Main

Range of Product	Altivar
Bus type	Modbus
Accessory / separate part category	Connection accessory
Accessory / Separate Part Type	T-junction box
Accessory / separate part destination	Modbus network
Cable length	3.28 ft (1 m)
Quantity per Set	Set of 1

Complementary

Complementary	
Range compatibility	Altivar 61Q
	Altistart 22
	Altivar 21
	Altistart 48
	Altivar Machine ATV340 except Sercos drives
	Altivar 31C
	Harmony GTO
	Altivar 61
	Altivar Process ATV600
	Modicon LMC058
	Altivar 12
	Altivar Easy 610
	Altivar 71
	Modicon M238
	Altivar Machine ATV320
	Altivar 312
	Altivar 212
	Modicon M258
	Altivar 32
	Altivar 71Q
	Lexium SD3
	Harmony XBT GT
	Zelio Logic
	Altivar Easy 310
	Altivar 31
	Altivar Process ATV900
Communication Port Protocol	Modbus
Electrical connection	1 male connector RJ45
	2 female connectors RJ45
Net Weight	0.46 lb(US) (0.21 kg)

Ordering and shipping details

Category	18062 - MISC. ALTIVAR/ALTISTART CABLES, CONNECTORS	
Discount Schedule	CP1G	
GTIN	3389110400526	
Nbr. of units in pkg.	1	
Package weight(Lbs)	2.57 oz (73 g)	
Returnability	Yes	
Country of origin	CN	

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	1.18 in (3 cm)	
Package 1 width	4.33 in (11 cm)	
Package 1 Length	4.53 in (11.5 cm)	
Unit Type of Package 2	S03	
Number of Units in Package 2	60	
Package 2 Weight	11.14 lb(US) (5.055 kg)	
Package 2 Height	11.81 in (30 cm)	
Package 2 width	11.81 in (30 cm)	
Package 2 Length	15.75 in (40 cm)	
Unit Type of Package 3	P06	
Number of Units in Package 3	480	
Package 3 Weight	112.80 lb(US) (51.164 kg)	
Package 3 Height	30.31 in (77 cm)	
Package 3 width	23.62 in (60 cm)	
Package 3 Length	31.50 in (80 cm)	

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	[™] REACh Declaration	
REACh free of SVHC	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEL RoHS Declaration	
Toxic heavy metal free	Yes	
Mercury free	Yes	
RoHS exemption information	€Yes	
China RoHS Regulation	China RoHS Declaration	

Contractual warranty

Warranty	18 mor	ths