

## Cat5e 350 MHz Snagless Molded Ethernet Cable (RJ45 M/M) - Gray, 125-ft.

MODEL NUMBER: N001-125-GY



### Description

Tripp Lite's 125-ft. gray snagless category 5e (Cat5e) patch cable has 2 snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair Solid Conductor UTP for improved long run performance, and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Standard category 5e patch cables are also available.

### Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 125-ft. Color: gray Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair Solid UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)

## Specifications

OVERVIEW	
UPC Code	037332041951
Technology	Cat5/5e

### Highlights

- Cabling for Category 5 (Cat5) and 5e (Cat5e) applications
- Solid Conductor wire for long distance performance
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 350 MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 5e, draft 11)

### System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

### Package Includes

- 125-ft. Gray Snagless Cat5e Patch Cable

PHYSICAL	
Color	Gray
Cable Shielding	UTP
Wire Type	Solid
Cable Length (ft.)	125
Cable Length (m)	38.11
Cable Length (in.)	1500
Cable Length (cm)	3810
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 2.00
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 5.08
Shipping Weight (lbs.)	2.80
Shipping Weight (kg)	1.27
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Snagless Connector	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty