

SFP+ 10Gbase-CU Passive Twinax Copper Cable, SFP-H10GB-CU1-5M Compatible, Black, 5 ft. (1.52 m)

MODEL NUMBER: **N280-005-BK**



Features

- 1.5 m. (5 ft.) 30Awg SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU1-5M (See the Support tab on this web page for additional cross references)
- Use in 10Gbps Ethernet and Fibre Channel applications
- 100ohm Twinaxial cable, Diecast metal shells, pull-to-release latching
- Support for 1x, 2x, 4x and 8x Fiber Channel data rates
- Hot-Pluggable SFP 20PIN footprint
- Low power consumption

Highlights

- 1.5 m. (5 ft.) 30AWG SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU1-5M
- Low Cost alternative to Fiber Optic

System Requirements

SFP+ Direct Attach Cable (DAC)
Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:

QLOGIC * EMULEX * JUNIPER *
ARISTA * IBM * DELL * EXTREME
EMC * BROADCOM * FINISAR *
VOLTAIRE * CISCO

CONFIRMED EQUIPMENT LIST (

*ensure the latest firmware and software is installed)
CISCO NEXUS *
CISCO CATALYST *
CISCO CATALYST 3750x
CISCO CATALYST 2960
CISCO CATALYST 3500
CISCO CATALYST 3550
CISCO NEXUS 5010
ARISTA 70505-64
QUANTA T3048
EXTREME X250E
JUNIPER EX3200

NOT COMPATIBLE TO 3RD
PARTY CABLES: HP and
BROCADE

Package Includes

- 1.5 m. (5 ft.) 30Awg SFP+ High Speed Passive Copper 10Gbps

Cable

Specifications

OVERVIEW	
UPC Code	037332178138
Cable Type	Passive
Compatible Brand	Arista; Broadcom; Cisco; Dell; EMC; Emulex; Extreme; Finisar; IBM; Juniper; QLogic; Voltaire
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	4.2mm
Wire Gauge (AWG)	30
Cable Length (ft.)	5
Cable Length (m)	1.52
Cable Length (in.)	60
Cable Length (cm)	152.4
Minimum Bend Radius	23mm
Shipping Dimensions (hwd / in.)	12.00 x 10.50 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 26.67 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Operating Humidity Range	5% to 85% RH
Storage Humidity Range	5% to 85% RH
COMMUNICATIONS	
Network Compatibility	10 Gbps
IEEE Standards Supported	802.3BA
CONNECTIONS	

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	SFP+ (MALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.