

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to 4xInfiniband (SFF-8470), 2M (6.56 ft.), TAA

MODEL NUMBER: \$520-02M



Highlights

- Hi-Performance 2 Meter SAS External Cable
- Mini-SAS SFF-8088 (iSAS) to SFF-8470
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

 SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

• 2 Meter SAS External SFF-8088 to SFF-8470 Cable

Features

- External SAS Cable, Mini-SAS SFF-8088 (iSAS) to SFF-8470 2 Meter
- Made with High-Performance Infiniband Cable
- Supports data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connector and SFF-8088 connector in die cast zinc housing for durability
- · RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW		
UPC Code	037332151957	
Technology	SAS	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	6.6	
Cable Length (m)	2.01	
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 8.50	
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 21.59	



Shipping Weight (lbs.)	0.50	
Shipping Weight (kg)	0.23	
CONNECTIONS		
Side A - Connector 1	SFF-8088	
Side B - Connector 1	SFF-8470	
STANDARDS & COMPLIANCE		
Product Compliance	Trade Agreements Act (TAA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.