

Specification Sheet

Part Number: PBM0M4



Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.

The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, Black, 1000/pkg

Article Number 151-00229

Type PBM

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.

Short Description Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, Black, 1000/pkg

Global Part Name PBM-PA66-BK

Length L (Metric)	10.7
Width W (Imperial)	0.26
Width W (Metric)	6.6
Cable Ties	T18 - T50
Height H (Imperial)	.40
Height H (Metric)	10.20
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Panel Thickness Min (Imperial)	0.118
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.29
Mounting Hole Diameter D (Metric)	6.25 - 6.55 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.29

Mounting Hole Diameter D Max (Metric)	6.55
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)