


Product data sheet

Specifications

Cable duct - 75 x 75 mm - without cover - grey



AK2GD7575

Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey RAL 7030)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	2.95 in (75 mm)
Net weight	2.29 lb(US) (1.04 kg)
Total number of wires	400

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.95 in (7.5 cm)

Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	2.36 lb(US) (1.072 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Height	42.52 in (108.0 cm)
Package 2 Width	79.13 in (201.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	831.14 lb(US) (377.0 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	5.71 in (14.5 cm)
Package 3 Width	6.10 in (15.5 cm)
Package 3 Length	79.13 in (201.0 cm)
Package 3 Weight	19.84 lb(US) (9.0 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)