SIEMENS

Data sheet

6XV1840-2AU10

| product description | Standard bus cable (4 wires), preferred length, not assembled |
|--|--|
| | Industrial Ethernet FC TP standard cable GP TP installation cable for Connection to IE FC RJ45 2x2, for universal use, CAT 5, 1000 m. |
| suitability for use | Standard cable with rigid cores for fast installation |
| cable designation | 2YY (ST) CY 2x2x0,64/1,5-100 GN SF/UTP |
| wire length | 1000 m |
| electrical data | |
| attenuation factor per length | |
| at 10 MHz / maximum | 0.052 dB/m |
| • at 100 MHz / maximum | 0.195 dB/m |
| impedance | |
| • at 1 MHz 100 MHz | 100 Ω |
| relative symmetrical tolerance | |
| of the characteristic impedance at 1 MHz 100 MHz | 15 % |
| transfer impedance per length / at 10 MHz | 10 mΩ/m |
| loop resistance per length / maximum | 115 mΩ/m |
| operating voltage | |
| RMS value | 80 V |
| NVP value in percent | 66 % |
| mechanical data | |
| number of electrical cores | 4 |
| design of the shield | Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires |
| type of electrical connection / FastConnect | Yes |
| core diameter | |
| of AWG22 insulated conductor | 0.64 mm |
| outer diameter | |
| of inner conductor | 0.64 mm |
| • of the wire insulation | 1.5 mm |
| • of the inner sheath of the cable | 3.9 mm |
| of cable sheath | 6.5 mm |
| symmetrical tolerance of the outer diameter / of cable sheath | 0.2 mm |
| material | |
| of the wire insulation | polyethylene (PE) |
| • of the inner sheath of the cable | PVC |
| of cable sheath | PVC |
| color | |
| of the insulation of data wires | white/yellow/blue/orange |
| of cable sheath | green |
| bending radius | |

| with single bend / minimum permissible | 19.5 mm |
|--|--|
| with single bend / minimum permissible with multiple bends / minimum permissible | 49 mm |
| tensile load / maximum | 150 N |
| weight per length | 61 kg/km |
| ambient conditions | |
| ambient temperature | |
| during operation | -40 +75 °C |
| during storage | -40 +75 °C |
| during transport | -40 +75 °C |
| during installation | -40 +60 °C |
| • note | Electrical properties measured at 20 °C, tests according to DIN VDE 0472 |
| class of burning behaviour / according to EN 13501-6 | Eca |
| chemical resistance | |
| • to mineral oil | oil resistant according to IEC 60811-2-1 (4 h / 70°C) |
| • to grease | Conditional resistance |
| • to water | conditional resistance |
| radiological resistance / to UV radiation | resistant |
| product features, product functions, product component | s / general |
| product feature | |
| halogen-free | No |
| • silicon-free | Yes |
| wire length / for Industrial Ethernet | |
| with 100BaseTX | 100 m |
| standards, specifications, approvals | |
| UL/ETL listing / 300 V Rating | Yes; c(ETL)us / CMG / (ETL)us PLTC/ ITC / Sun Res |
| UL/ETL style / 600 V Rating | Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2 |
| certificate of suitability | |
| EAC approval | Yes |
| CE marking | Yes |
| standard for structured cabling | Cat5e |
| Marine classification association | |
| American Bureau of Shipping Europe Ltd. (ABS) | No |
| • French marine classification society (BV) | No |
| Det Norske Veritas (DNV) | No |
| Germanische Lloyd (GL) | No |
| Lloyds Register of Shipping (LRS) | No |
| Nippon Kaiji Kyokai (NK) | No |
| Polski Rejestr Statkow (PRS) | No |
| reference code | |
| according to IEC 81346-2 | WG |
| according to IEC 81346-2:2019 | WGB |
| further information / internet-Links | |
| Internet-Link | |
| to web page: selection aid TIA Selection Tool | http://www.siemens.com/tia-selection-tool |
| to website: Industrial communication | http://www.siemens.com/simatic-net |
| to website: Industry Mall to website: Information and Download Contar | https://mall.industry.siemens.com |
| to website: Information and Download Center to website: Selection guide for eables and | http://www.siemens.com/industry/infocenter |
| to website: Selection guide for cables and connectors | https://sie.ag/2QdlxcP |
| • to website: Image database | http://automation.siemens.com/bilddb |
| • to website: CAx-Download-Manager | http://www.siemens.com/cax |
| to website: Industry Online Support | https://support.industry.siemens.com |
| last modified: | 10/30/2021 🖸 |