

#### RFEC-1

High quality low loss CFD400 cable suitable for outdoor installation and weather extreme conditions.

Length 1 meter with connectors M-Female to RP-SMA Male



Fully compatible with technologies, products and services by













### **Features**


- ✓ Robust construction for outdoor usage
- ✓ Perfect connector match with RF Explorer high performance antennas and Helium hotspots
- ✓ Very low insertion loss

## **Specification**


Frequency Range	0-6000MHz
Length	1 meter ±30mm
Impedance	50Ω
VSWR	Typical 1.1 @ 900MHz ≤1.5 max @ 6GHz
Insertion Loss	Typical 0.15db @ 900MHz ≤1.5dB max @ 6GHz
Capacitance	76pF/m
Velocity of Propagation	85%
Connectors	Type N Male/Jack Type RP SMA Male
Insulation Resistance	> 1,000 MΩ
Bend Radius	Min 25.4mm
Voltage Breakdown	2.5KV
External Cable Diameter	10.3mm
Connectors	Type N Female Type RP-SMA Male
Mating Cycles	> 500
Jacket Material	PE
Conductor Material	Copper
Binder Material	Aluminum/PE Tape
Braid Material	Tinned copper wire
Operation Temperature	-30°C to +65°C
Environmental	RoHS



### **VSWR**



## **Insertion Loss**





# **Mechanical Specifications**

