


# Hospital-Grade Extension Cord, NEMA 5-15P to NEMA 5-15R - Green Dot, 13A, 125V, 16 AWG, 15 ft. (4.57 m), Gray

MODEL NUMBER: P022-015-GY-HG











Hospital-grade extension cord connects two devices with 5-15P-HG/5-15R-HG power connectors in a hospital or other medical facility.

#### **Features**

Hospital-Grade Extension Cord is a Safe Solution for Medical Facilities This hospital-grade power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment within a healthcare facility. It features a NEMA 5-15R-HG end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

**Designed and Tested to Strict Hospital-Grade Standards**This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime**This extension cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

### **Highlights**

- Adds 15-ft. (4.57 m) to your existing power connection to provide flexibility in placing devices
- Medical power cord replaces or upgrades power cord provided by manufacturer
- 5-15P-HG plug connects to AC power; 5-15R-HG end connects to device's input cord
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

#### **Applications**

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 15-ft. (4.57 m) away in a hospital environment
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

#### **Package Includes**

 P022-015-GY-HG Hospital-Grade Extension Cord, 5-15P-HG to 5-15R-HG, 15-ft. (4.57 m), Gray

## **Specifications**

OVERVIEW		
UPC Code	037332200112	
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU	
Country/Region	North America	
INPLIT		
	13	
INPUT  Maximum Input Amps	13	



Voltage Compatibility (VAC)	125	
PHYSICAL		
Plug Color	Gray	
Cable Jacket Color	Gray	
Cable Jacket Material	PVC	
Cable Jacket Rating	FT2	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	9mm	
Number of Conductors	3	
Wire Gauge (AWG)	16	
Wire Gauge (OD - mm²)	1.31	
Cable Length (ft.)	15	
Cable Length (m)	4.57	
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50	
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27	
Shipping Weight (lbs.)	1.24	
Shipping Weight (kg)	0.56	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	20% to 80% RH	
Storage Humidity Range	20% to 80% RH	
CONNECTIONS		
Side A - Connector 1	NEMA 5-15P-HG	
Side B - Connector 1	NEMA 5-15R	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	No	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		



Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.