


# Product data sheet

Specifications

## Cable duct - 55 x 30 mm - without cover - blue



AK2GA35

### Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

### Complementary

Colour	Blue RAL 5000)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	2.17 in (55 mm)
Length	78.74 in (2000 mm)
Width	1.18 in (30 mm)
Net weight	1.76 lb(US) (0.8 kg)
Total number of wires	110

### Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660 NF C 68-102

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

<b>Package 1 Height</b>	3.35 in (8.5 cm)
<b>Package 1 Width</b>	4.33 in (11.0 cm)
<b>Package 1 Length</b>	78.74 in (200.0 cm)
<b>Package 1 Weight</b>	22.05 oz (625.0 g)
<b>Unit Type of Package 2</b>	PAL
<b>Number of Units in Package 2</b>	320
<b>Package 2 Height</b>	30.31 in (77.0 cm)
<b>Package 2 Width</b>	110.24 in (280.0 cm)
<b>Package 2 Length</b>	47.24 in (120.0 cm)
<b>Package 2 Weight</b>	440.92 lb(US) (200.0 kg)
<b>Unit Type of Package 3</b>	CAR
<b>Number of Units in Package 3</b>	8
<b>Package 3 Height</b>	4.33 in (11.0 cm)
<b>Package 3 Width</b>	33.46 in (85.0 cm)
<b>Package 3 Length</b>	78.74 in (200.0 cm)
<b>Package 3 Weight</b>	11.02 lb(US) (5.0 kg)

## Offer Sustainability

<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>RoHS exemption information</b>	<a href="#">Yes</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)