

Specification Sheet

Part Number: 161-05089



Sheathing allows flexible routing and lead-out of cables
The inner edges are beveled preventing damage to cables
Sheathing is reusable and resistant to most chemicals
Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.75" Diameter, PA6, Black, 500ft/roll

Article Number	161-05089
Type	4N0H
Color	Black (BK)
Quantity Per	reel
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.75" Diameter, PA6, Black, 500ft/roll
Global Part Name	4N0H-PA6-BK

Length L (Imperial)	500.0
Length L (Metric)	152.4
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.5
Bundle Diameter Min (Metric)	12.7
Bundle Diameter Max (Imperial)	5.0
Bundle Diameter Max (Metric)	127.0
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.05
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.032
Wall Thickness WT (Metric)	0.81
Material	Polyamide 6 (PA6)
Material Shortcut	PA6

Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	152.40
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)