




UNIT: mm



CABLE WHITE PRINT
 HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
 E189529 **RA** AWM STYLE 2725 80° C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
 1. 100% short, open, miswire test
 2. Conduct resistance: 5 Ohm(max)
 3. Insulation resistance: 5Mohm(min)
 4. dielectric test: DC 300V

③	PE BAG	1/5	CLEAR SIZE: 360*380*40.05mm PRINT BLACK "MADE IN CHINA" + "5PCS".
⑦	PE BAG	1	CLEAR SIZE: 150*280*40.05mm PRINT BLACK "MADE IN CHINA" + "1PC".
⑥	TIE	1	BLACK L=120mm
③	OUT JACKET	6g	BLACK PVC-40P (MOULD NO.: MW-65)
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO.: MW-40)
③	CABLE	1	BLACK USB2.0 UI2725 28#/1P+24#/2C+A+B OD: 4.7mm L=5000±20mm
⑦	CONN	Iset	USB2.0 B MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	Iset	USB2.0 A MALE SHELL: NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE

CnC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1030-BL-00500
DECIDED		DATE	2012-02-14
VERSIONS/EDITION	A/0	PROJECTION	

A

B

C

D

4

3

2

1

A

B

C

D