SIEMENS

Data sheet

6ES7900-0EA00-0XA0

AC IEC cable, Italy Type L and others, 180° male to 180° female (3-pole, C13) for Italy, in part Africa for devices with corresponding interface, length und further information, Quantity and content: see technical data



Figure similar

General information	
Product type designation	Cable for non-heating apparatus
Interfaces	
Interfaces/bus type	Line-side, country-specific connector: Type L (CEI 23-50)
Device-side interface	
 Number of pins device-side 	3; Female, C13 connector type
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes; N11419
KC approval	No
EAC (formerly Gost-R)	No
000	Yes
RoHS conformity	Yes
Ambient conditions	
Suited for indoor use	Yes; Max. 10 A
Ambient temperature during operation	
• min.	-10 °C
• max.	50 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	85 °C
Relative humidity	
• Operation, max.	90 %
Cables	
Cable length	3 m
Color of cable sheath	Black
Weights	
Weight, approx.	255 g
Scope of supply	
Delivery quantity in pieces	1; AC cable for IT
Other	
Merchandise	Yes; I/3G-H05VVF3G100-C13/3,00M SW9005
Manufacturer name	FELLER GmbH
Manufacturer's address	Wärndorferstraße 3, 2525 Günselsdorf, Austria; email: sales@feller- at.com
Target devices	Suitable for all appropriate DC interfaces
Note:	http://www.feller-at.com
Usable in the following products	

Product 1

last modified:

6AV6671-5CN00-0AX3

12/18/2020 🖸