TRIPP·LITE by **FATON**

Heavy-Duty USB-A to USB-C Cable, USB 2.0, UHMWPE and Aramid Fibers, (M/M), Gray, 3 ft. (0.91 m)

MODEL NUMBER: U038-003-GY-MAX







Durable USB cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

Features

Heavily Reinforced USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C DeviceThis heavy-duty USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook, Ultrabook, Chromebook or other USB-C device to the USB-A port on a computer, car charger or wall charger. It allows you to charge and power your USB-C device, while simultaneously synching and transferring data at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Constructed Using UHMWPE and Bulletproof Aramid Fiber Designed to LastCharging cables used with mobile devices are often pulled, strained and generally abused, sometimes to the point of failure. To counter the stress of daily abuse, the super-robust U038-003-GY-MAX is constructed using UHMWPE and Aramid fiber to reinforce the conductors inside the cable. The double-braided nylon jacket helps maintain top performance and long life, while the enhanced UHMWPE and Aramid protection stands up to the strain of rigorous and frequent use. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time. The cord's three-foot length helps reduce cable clutter.

1000 Eaton Boulevard Cleveland, OH 44122 United States

Highlights

- Engineered using UHMWPE and Aramid fiber to stand up to frequent and rigorous use
- Extra-strong cable construction helps prevent fraying and loose cable connectors
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Integral strain relief helps cable move freely without stress or cracking
- Reversible USB-C plug connects in either direction for immediate no-fuss use

Applications

- Charge and sync your MacBook, Chromebook or other USB-C device from a USB computer or wall charger up to 3 ft. away
- Transfer data between an external hard drive and your USB-C notebook or computer
- Replace a cable that became frayed or inoperable due to frequent use
- · Carry in your laptop bag, backpack or briefcase as a durable spare cable

System Requirements

- Device or charger with USB-A port
- Device with USB-C port

Package Includes

 U038-003-GY-MAX Heavy-Duty USB-A to USB-C Cable (M/M), Gray, 3 ft. (0.9 m)

Specifications

OVERVIEW	
UPC Code	037332241320
Technology	USB 2.0 (High Speed)

TRIPP-LITE

Cable Type	Passive	
INPUT		
Maximum Input Amps	3	
POWER		
USB Power Delivery (PD) Charging Support	No	
CHARGING		
Total Charging Watts	15	
PHYSICAL		
Material of Construction	PVC, UHMWPE, Aramid	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	3.4 mm	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Cable Length (in.)	36	
Cable Length (cm)	91.4	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.07	
Shipping Weight (kg)	0.03	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Packaging Type	Polybag	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 176°F (-20° to 80°C)	
Relative Humidity	0% to 90% RH, Non-Condensing	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
Power Provided to Connected Device(s)	15W (5V/3A)	
CONNECTIONS		

TRIPP-LITE

Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	USB C (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
Connector Style	Straight	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
Data Transfer Rate	480 Mbps	
Angled Plug	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
	·	

TRIPP-LITE

© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.