



* 所有原材料, 生产制程, 电镀必须符合ROHS要求


1.SPECIFICATIONS
 INSULATION RESISTANCE: 500M min. AT DC 500V DC
 WITHSTANDING VOLTAGE: 250V AC rms FOR 1 MINUTE
 CONTACT RESISTANCE: 100M max. AT 10mA/20mV max
 CURRENT RATING: 0.5A
 VOLTAGE RATING: 5.0 vrms
 OPERATING TEMP.RANGE: -55 C+85 C
 MATING CYCLES: 5000 INSERTIONS

2.MATERIAL:
 INSULATOR: H-TEMPERATURE PLASTIC,UL 94V-0,
 COLOR:BLACK
 TERMINAL: COPPER ALLOY,T=0.15mm
 SHELL: STAINLESS STEEL,T=0.15mm

3.FINISH:
 TERMINAL:50 μ m² min NICKEL UNDERPLATED ON ALLOYER,GOLD PLATING
 ON CONTACT ARER, FLASH GOLD ON SOLDER TAIL
 SHELL:50 μ m² NICKEL UNDERPLATED ON ALLOYER, GOLD FLASH ON SOLDER LATCH



RECOMMENDED PCB LAYOUT



PIN#	Name
C1	VCC
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	VPP
C7	I/O
C8	Reserved

Bossie (博锡)

DIMENSIONS INIT: mm UNLESS OTHERWISE SPECIFIABLE DIMENSION TOLERANCE X.X ± 0.25 X.XX ± 0.10 X.XXX ± 0.05 ANGULAR: ± 1°	PRODUCT NAME : 自弹式 MiniSIM卡 卡座 6+2	DRAWING: DATE:
	PRODUCT NO. : BX-SIM-1.85H62PJ	CHECK: DATE:
DRAWING NO. :	APPROVED: DATE:	SCALE: 1:1 DWG ID: r r REV.: A PAGE: 1 of 1

REVISION NO.	FCR NO.	DESCRIPTION	MARK	DATE