



线路板开孔尺寸  
P.C.B LAYOUT



按点示意图  
SCHEMATIC



主要技术特性:

- 1. 额定电负荷: DC 12V, 3A;
- 2. 接触电阻:  $\leq 30m\Omega$ ;
- 3. 绝缘电阻:  $\geq 100M\Omega$ ;
- 4. 耐 压 : AC500V(50-60HZ) 1min;
- 5. 插 拔 力: 2.94-29.4N;
- 6. 寿 命: 5,000次。

主要技术要求

- 1. 未注线性公差:
  - 0.0-10.0mm  $\pm 0.20mm$
  - 10.0-20.0mm  $\pm 0.25mm$
  - 20.0-50.0mm  $\pm 0.30mm$
- 2. 外观应良好, 无锈蚀、裂痕、电镀不良等现象。

Model No.	DC-005-A	DC-005-B
PIN $\phi(X)$	2.0	2.5

6	后 盖	1	PBT	(黑)
5	基 座	1	PBT	(黑)
4	插 针	1	H59黄铜棒	铜锡
3	簧 片	1	磷铜带T=0.25	银
2	弯 片	1	H62黄铜带T=0.35	银
1	平 片	1	H62黄铜带T=0.50	银
序号	名 称	数量	材 料	镀 涂



COPYRIGHT RESERVED, PLEASE DO NOT COPY.

PART NAME		DC电源插座		DRAWING		Zhou qi		DWG.No.	
PART NO.		BX-DC-J-N2.5W6.3		CHECK				REV. A1	
UNIT :	TOLERANCE OTHERWISE	UP TO 5	$\pm 0.2$	ANGLE	APPROVAL	DATE		23/05/21	
		ABOVE 5~30	$\pm 0.3$			PAGE		1 OF 1	
mm		ABOVE 30	$\pm 0.5$	$0^{\circ}\pm 3^{\circ}$	SCALE	2:1			