


| Pin | A | B | C |
|-----|-------|-------|-------|
| 2 | 1.25 | 7.50 | |
| 3 | 2.50 | 8.75 | |
| 4 | 3.75 | 10.00 | 2.50 |
| 5 | 5.00 | 11.25 | 3.75 |
| 6 | 6.25 | 12.50 | 5.00 |
| 7 | 7.50 | 13.75 | 6.25 |
| 8 | 8.75 | 15.00 | 7.50 |
| 9 | 10.00 | 16.25 | 8.75 |
| 10 | 11.25 | 17.50 | 10.00 |
| 11 | 12.50 | 18.75 | 11.25 |
| 12 | 13.75 | 20.00 | 12.50 |
| 13 | 15.00 | 21.25 | 13.75 |
| 14 | 16.25 | 22.50 | 15.00 |
| 15 | 17.50 | 23.75 | 16.25 |
| 16 | 18.75 | 25.00 | 17.50 |



技术参数
 间距: 1.25
 温度范围: -25~+85°C
 额定电压: 125V AC, DC
 额定电流: 1.0A AC, DC
 接触电阻: 20mΩ
 绝缘电阻: 100MΩ
 耐压: 500V AC/minute

线性公差 / General Tolerance
 X ±0.2
 X.X ±0.1
 X.XX ±0.05
 角度公差 / Angle Tolerance
 X° ±5.0°
 X.X° ±3.0°
 X.XX° ±1.0°

视角 / Projection



| 标记 | 变更内容 | 签名 | 年月日 |
|----|------|----|-----|
| 绘图 | | | |
| 审核 | | | |
| 工艺 | | 批准 | |

材料 / Material

- ①塑座: LCP 本色
- ②接触针: 黄铜 (镀锡)
- ③焊片: 黄铜 (镀锡)

阶段标记 版本 比例

2.0 1:1

共 1 张 第 1 张

B Bossie (博锡)

品名 / ProduceName

MX1.25 卧贴 5P

型号 / Model

BX-MX1.25-5PWT