







标记 MARK	更改内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE
e				



← F向



此凸点只限10PIN以上的产品有，
2-10PIN的产品均无此凸点




技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、额定电流 Current rating:2.0A AC,DC
- 3、额定电压 Voltage rating: 250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻 Insulation resistance:≥1000MΩ
- 7、耐压 Withstand voltage:500V AC/minute
- 8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

线数	型号	尺寸				
		A	B	C	D	E
2	SH20004-2Y	2.00	4.70	2.30	1.00	0.60
3	SH20004-3Y	4.00	6.70	2.30	1.00	0.60
4	SH20004-4Y	6.00	8.70	4.30	1.70	1.00
5	SH20004-5Y	8.00	10.70	4.30	1.70	1.00
6	SH20004-6Y	10.00	12.70	8.30	5.90	1.95
7	SH20004-7Y	12.00	14.70	10.30	7.90	1.95
8	SH20004-8Y	14.00	16.70	12.30	9.90	1.95
9	SH20004-9Y	16.00	18.70	12.30	9.90	1.95
10	SH20004-10Y	18.00	20.70	12.30	9.90	1.95
11	SH20004-11Y	20.00	22.70	16.30	13.90	1.95
12	SH20004-12Y	22.00	24.70	16.30	13.90	1.95
13	SH20004-13Y	24.00	26.70	16.30	13.90	1.95
14	SH20004-14Y	26.00	28.70	16.30	13.90	1.95
15	SH20004-15Y	28.00	30.70	16.30	13.90	1.95
16	SH20004-16Y	30.00	32.70	16.30	13.90	1.95



TOLERANCE UNLESS OTHERWISE SPECIFIED		*: Inspection Item		Bossie (博锡)			
.X±0.30	X.° ±1°	NO.	:Cp/Cpk and SPC Control Item	名称	HY2.0胶壳-4Pin		
.XX±0.20	.X° ±			材料	PA66 (CM3004-V0)	编号	BX-HY2.0-4PJk
.XXX±0.10	.XX° ±			料厚		单位	mm
制图		料宽		比例	1:1		
审核		日期		角法	第一角法		
批准				版本	A		
				规格书			