``		PROPRIETARY INFORMATION:			1	REVISION			
		PROPRIETARY OF GLOBTEK, INC. ANY	REPRODUCTION, DISCLOSURE OR IN PART, IS HEREBY		R REV				
		USE OF THIS DRAWING, IN WHOLE OR PROHIBITED EXCEPT AS SPECIFIED IN			А	INITIAL RELEASE, RFS. 26850, RC	08/07/17	BS	
		L	2000+70,-20						
	P4				<u></u>		I ±0.5		
P1 USB-TYPE-A				FEMALE BARREL 5.5*2.5*11 mm CENTER POSITIVE					
	Pin ASSIGNMENT					Twist Tie (2pls)	RELEASED By N.Frost at 2:05 pm, Aug	07, 2017	
	2 White 3 Green (NO CONNECTE (NO CONNE	5*11 BARREL CENTER ED TOGETHER ECTION TO BARREL)DC BARREL OUTSIDE			60.0Min	85.0 Min.	75.0 max.	rdous Substances	
TITLE DESCRIPTION							vi sailam	フリ	
HEAT SHRINK TUE	BE 0.D. 0.8, CC	130.0 Max							
CABLE	UL2725 BLACK 28 AWG TWISTED PAIR + 2X 22 AWG, SHIELDED		DASH	r					
USB TYPE A PLUC	G CONTACT GOL	NO.	PART NO	REV.	DESCRIPTION		NOTES		
				TABULATION BLOCK					
					TOLERANCES: DECIMALS ANGULAI .xx +/- 0.1 +/- 1* .xxx +/005	www.globtek.com	186 Veterans Dr. Northva Tel. 201-784-1000 Fax 2	le, NJ 07647 01.784.0111	
G	Foot Note: Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applica- ole UL,CSA or EN Standards for proper installation instruction.	mission critical components in life support, haz- ardous environment, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.	INIT.BY: RC	DATE: MILLIMETERS ANGULAR .xx +/- 0.3 +/- 1' 08/07/17 .xx +/013 MILLIMETERS ANGULAR .xx +/- 0.3 +/- 1' UWG TITLE: DETACHABLE USB CORD USB TYPE-A TO FEMALE BA		CORD MALE BARREL			
Contents of this document pro are subject to change without occ			DRAWN: NF	DATE: 08/07/17	FSCN No.: SIZE G, CC A			REV. A	
			APRVD: MK	DATE: 08/07/17	SCALE: NONE	PART NO: USBA2M0LCP-C	HG(R)	SHEET 1/1	