


Specification Sheet

Part Number: MMB00C2



Masonry Mounts provide a permanent solution when fastening wire and cables to masonry surfaces.

The mounts have easy installation into predrilled holes allowing for faster use.

Article Number 151-29800

Type MMB0

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton Masonry Mounts provide a permanent method of attaching wire and cable to masonry surfaces. Masonry mounts simply tap into predrilled holes and can be used for indoor and outdoor applications.

Short Description Masonry Cable Tie Mount, 1.185" Long, 0.188" Hole Dia, 0.18" Max Cable Tie Width, PA66STHS,Black,100/pkg

Global Part Name MMB0-PA66STHS-BK

Length L (Imperial)	1.185
Length L (Metric)	30.1
Fixation Method	with Fir Tree (Mounts)
Width W (Imperial)	0.355
Width W (Metric)	9.0
Cable Ties	T18 - T50
Height H (Imperial)	.35
Height H (Metric)	8.90
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Panel Thickness Min (Imperial)	1.0
Panel Thickness Min (Metric)	25.4
Panel Thickness Max (Metric)	25.4
Mounting Hole Diameter D (Imperial)	0.188
Mounting Hole Diameter D (Metric)	4.7 mm
Mounting Hole Diameter D Max (Metric)	4.7

Material	Polyamide 6.6, super tough, heat stabilized (PA66STHS)
Material Shortcut	PA66STHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).