

## Internal SAS Cable, 4-in-1 32Pin (SFF-8484) to 32Pin (SFF-8484) Cable, 1M (3-ft.)

MODEL NUMBER: **S500-01M**



### Highlights

- 32-pin SFF-8484 to SFF-8484 Internal SAS Cable
- Supports data rates up to 6.0Gbs
- Straight backshell configuration

### System Requirements

- SAS Host Bus Adapter and Backplane with SFF-8484 mating connector

### Package Includes

- 1-Meter Internal SAS 4-in-1 SFF-8484 to SFF-8484 Cable

### Description

Tripp Lite's 32-pin SFF-8484 to SFF-8484 Internal SAS (Serial Attached SCSI) cable is ideal for use with SAS controllers to SAS disk drive back planes. High-performance cable provides differential pair signaling with less than 5ps/m in pair skew, improved EMI protection, and 3.0Gbs data rate with rates up to 6.0Gbs. Thinner, flexible cable enables more efficient routing, with improved airflow and thermal mechanics. Configuration of storage devices is simplified. Tripp Lite's SAS assemblies are RoHS compliant and feature a

### Features

- Internal SAS 4-in-1 SFF-8484 to SFF-8484 Cable - 1 meter
- Supports data rates of up to 6.0Gbs
- Thin, flexible cable for easy routing and increased airflow
- RoHS compliant

## Specifications

OVERVIEW	
UPC Code	037332138132
PHYSICAL	
Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27

Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
<b>CONNECTIONS</b>	
Side A - Connector 1	SFF-8484
Side B - Connector 1	SFF-8484
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty