

# Product data sheet

Specifications



## connection cable - Twido discrete I/O to Telefast - 2 m

ABFTP26MP200

! Discontinued on: 02 May 2022

! Discontinued

### Main

|                                       |   |
|---------------------------------------|---|
| Range of product                      | Twido   |
| Accessory / separate part designation | Discrete I/O pre-formed cable                                     |
| Accessory / separate part type        | Connecting cable  |
| Accessory / separate part category    | Connection accessories  |
| Accessory / separate part destination | Discrete I/O  |
| Product specific application          | For application other than use of Advantys Telefast ABE7 sub-base |

### Complementary

|                       |   |
|-----------------------|---|
| Product compatibility | TWDLMDA20DTK<br>TWDLMDA40DTK  |
| Cable length          | 2 m   |
| AWG gauge             | AWG 28  |
| Cable cross section   | 0.08 mm <sup>2</sup>  |
| Electrical connection | 1 connector HE10 26 pin(s) Twido side<br>2 connectors HE10 20 pin(s) sensor or preactuator side |
| Net weight            | 0.5 kg  |

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type of Package 1       | PCE   |
| Number of Units in Package 1 | 1     |
| Package 1 Height             | 4 cm  |
| Package 1 Width              | 25 cm |
| Package 1 Length             | 20 cm |
| Package 1 Weight             | 247 g |

### Offer Sustainability

|                          |                                   |
|--------------------------|-----------------------------------|
| Sustainable offer status | Green Premium product             |
| REACH Regulation         | <a href="#">REACH Declaration</a> |

|                                   |   |
|-----------------------------------|---|
| <b>REACH free of SVHC</b>         | Yes   |
| <b>EU RoHS Directive</b>          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>   |
| <b>Toxic heavy metal free</b>     | Yes   |
| <b>Mercury free</b>               | Yes   |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a>  |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>   |
| <b>Circularity Profile</b>        | <a href="#">End of Life Information</a>   |
| <b>WEEE</b>                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins   |
| <b>California proposition 65</b>  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

## Recommended replacement(s)