

一. 电气性能:

- 1-1. 额定电流: 3A AC DC
- 1-2. 接触电阻: $\leq 20\text{m}\Omega$
- 1-3. 绝缘电阻: $\geq 1000\text{M}\Omega$
- 1-4. 耐 压: 550V AC/Minute


二. 物理特性:

- 2-1. 操作温度: $-55^\circ\text{C} \sim 105^\circ\text{C}$
- 2-2. 焊接温度: $+250^\circ\text{C}$, 10s max

三. 材质:

- 3-1. 塑胶: PA6T (Red) UL94V-0
- 3-2. 插针: Brass/Gold plated

N=单排PIN数



P. C. B Layout

—		new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	2005FV-XXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:		X. ±0.25
			MODEL NAME	2005FV-XXP			X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15	ANGULAIR ±3
				FILE.NO.			