





RoHS

SPECIFICATIONS

Current rating: 1A AC, DC
 Voltage rating: 50V AC, DC
 Temperature range: -25°C ~ +85°C
 Insulation resistance: 500M Ω/ min.
 Withstanding voltage: 500V AC/ minute.
 Contact resistance: 20m Ω/ max.



P.C.B LAYOUT



版次	修訂內容	修訂者	修訂日期

PIN	PART No.	Dimension mm	
		A	B
2	A1001-FVS02	1.0	4.0
3	A1001-FVS03	2.0	5.0
4	A1001-FVS04	3.0	6.0
5	A1001-FVS05	4.0	7.0
6	A1001-FVS06	5.0	8.0
7	A1001-FVS07	6.0	9.0
8	A1001-FVS08	7.0	10.0
9	A1001-FVS09	8.0	11.0
10	A1001-FVS10	9.0	12.0
11	A1001-FVS11	10.0	13.0
12	A1001-FVS12	11.0	14.0
13	A1001-FVS13	12.0	15.0
14	A1001-FVS14	13.0	16.0
15	A1001-FVS15	14.0	17.0
16	A1001-FVS16	15.0	18.0
17	A1001-FVS17	16.0	19.0
18	A1001-FVS18	17.0	20.0
19	A1001-FVS19	18.0	21.0
20	A1001-FVS20	19.0	22.0

MATERIAL: PIN: PHOSPHOR BRONZE/TIN -PLATED
 WAFER : NYLON UL94V-0
 MATES WITH ZYA1001H SERIES SINGLE ROW HOUSING

項次	品名	規格說明	圓圖編號	用量
	TERMINAL			
	空主體			10F1
	接力片			

圖面編號	A1001FVS-ZY02	
一般公差	.X±0.15 .XX±0.05 ∠±1°	
頁次	10F1	
繪圖/日期		
設計/日期		
核對/日期		

深圳市連欣科技有限公司			
圖面名稱: 1.0 SMT 180° Wafer			
產品編號: XDWF-0180-**-P			
單位	mm	比例	版次 A/0