





RoHS

SPECIFICATIONS

Current rating: 1A AC, DC
 Voltage rating: 50V AC,DC
 Temperature range: -25°C ~ +85°C
 Insulation resistance: 500M Ω/ min.
 Withstanding voltage: 500V AC/ minute.
 Contact resistance: 20m Ω/ max.



P.C.B LAYOUT



版次	修訂內容	修訂者	修訂日期

PIN	PART No.	Dimension mm	
		A	B
2	A1001-FRS02	1.0	4.0
3	A1001-FRS03	2.0	5.0
4	A1001-FRS04	3.0	6.0
5	A1001-FRS05	4.0	7.0
6	A1001-FRS06	5.0	8.0
7	A1001-FRS07	6.0	9.0
8	A1001-FRS08	7.0	10.0
9	A1001-FRS09	8.0	11.0
10	A1001-FRS10	9.0	12.0
11	A1001-FRS11	10.0	13.0
12	A1001-FRS12	11.0	14.0
13	A1001-FRS13	12.0	15.0
14	A1001-FRS14	13.0	16.0
15	A1001-FRS15	14.0	17.0
16	A1001-FRS16	15.0	18.0
17	A1001-FRS17	16.0	19.0
18	A1001-FRS18	17.0	20.0
19	A1001-FRS19	18.0	21.0
20	A1001-FRS20	19.0	22.0

MATERIAL:PIN:PHOSPHOR BRONZE/TIN -PLATED
 WAFER :NYLON UL94V-0
 MATES WITH ZYA1001H SERIES SINGLE ROW HOUSING

項次	品名	規格說明	圓圖編號	用量
	TERMINAL			
	空主體			
	接力片			

圖面編號	A1001FRS-ZY01
一般公差	.X±0.15 .XX±0.05 <±1°
頁次	1OF1
繪圖/日期	
設計/日期	
核對/日期	

<p>深圳市连欣科技有限公司</p>			
<p>圖面名稱: 1.0 SMT 90° Wafer</p>			
<p>產品編號: XDWF-0910-**-P</p>			
單位	mm	比例	版次 A/0