



CKT	DIM A	DIM B	DIM C
2	1.00	2.50	4.00
3	2.00	3.50	5.00
4	3.00	4.50	6.00
5	4.00	5.50	7.00
6	5.00	6.50	8.00
7	6.00	7.50	9.00
8	7.00	8.50	10.00
9	8.00	9.50	11.00
10	9.00	10.50	12.00
11	10.00	11.50	13.00
12	11.00	12.50	14.00
13	12.00	13.50	15.00
14	13.00	14.50	16.00
15	14.00	15.50	17.00
16	15.00	16.50	18.00
17	16.00	17.50	19.00
18	17.00	18.50	20.00
19	18.00	19.50	21.00
20	19.00	20.50	22.00
22	21.00	22.50	24.00
24	23.00	24.50	26.00
26	25.00	26.50	28.00

**技术指标:**

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
  2. 温度范围: -25° C~85° C.
  3. 额定电压: 30V, AC/DC.
  4. 接触电阻: ≤0.02Ω.
  5. 绝缘电阻: ≥100MΩ.
  6. 额定电流:
- 适用电线型号: a. AWG#28:1.0A (per pin)  
 b. AWG#30:1.0A (per pin)  
 c. AWG#32:0.8A (per pin)

**深圳市连欣科技有限公司**

规格 (SIZE) **WAFER 1.00 Pitch 卧式带扣** 制图 (DIN)

料号 (DRAWING NO) **XDWF-1015WT-\*\*\*P** 审核 (APP)

比例 (SCALE) **1:1** 单位 (UNIT) **mm** 张数 (SHEET) **1** 版数 (REV) **OP 1**

一般公差 (TOLERANCES)  
 X ±0.50 XX ±1.0  
 Y ±0.20 YY ±0.50  
 ANGLES 2°

序号	项目	描述	备注
1	塑胶	LCP	
2	端子	黄铜	
3	焊片	黄铜	