





SECTION A-A

- SPECIFICATIONS**
- 1、Current Rating: 0.5A AC, DC
 - 2、Voltage Rating: 30V AC, DC
 - 3、Temperatuer Range: -25℃~ +85℃
 - 4、Contact Resistance: 30mΩ Max
 - 5、Insulation Resistance: 100mΩ Min
 - 6、Withstanding Voltang: 200V AC/minute
 - 7、Material: Wafer LCP UL94-V0
Qty/Reel: 4000 PCS



Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-0.8-2PWT-XX	0.80	3.80
3	XD-0.8-3PWT-XX	1.60	4.60
4	XD-0.8-4PWT-XX	2.40	5.40
5	XD-0.8-5PWT-XX	3.20	6.20
6	XD-0.8-6PWT-XX	4.00	7.00
7	XD-0.8-7PWT-XX	4.80	7.80
8	XD-0.8-8PWT-XX	5.60	8.60
9	XD-0.8-9PWT-XX	6.40	9.40
10	XD-0.8-10PWT-XX	7.20	10.20
11	XD-0.8-11PWT-XX	8.00	11.00
12	XD-0.8-12PWT-XX	8.80	11.80
13	XD-0.8-13PWT-XX	9.60	12.60
14	XD-0.8-14PWT-XX	10.40	13.40
15	XD-0.8-15PWT-XX	11.20	14.20
16	XD-0.8-16PWT-XX	12.00	15.00
17	XD-0.8-17PWT-XX	12.80	15.80
18	XD-0.8-18PWT-XX	13.60	16.60
19	XD-0.8-19PWT-XX	14.40	17.40
20	XD-0.8-20PWT-XX	15.20	18.20



GENERAL TOLERANCE			制图 DRAWING	01	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	0.8 单排 卧贴	版本 REV.	A
X.XX ±0.20			投影 Projection		产品料号 PART NO.	XD-0.8-NPWT-XX	单位 UNITS	mm
X.XXX ±0.10					材料 MATERIAL		页次 SHEET	1/1
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						