


SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Housing PBT UL94-VO

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-1.0-2Y	1.00	5.00
3	XD-1.0-3Y	2.00	6.00
4	XD-1.0-4Y	3.00	7.00
5	XD-1.0-5Y	4.00	8.00
6	XD-1.0-6Y	5.00	9.00
7	XD-1.0-7Y	6.00	10.00
8	XD-1.0-8Y	7.00	11.00
9	XD-1.0-9Y	8.00	12.00
10	XD-1.0-10Y	9.00	13.00
11	XD-1.0-11Y	10.00	14.00
12	XD-1.0-12Y	11.00	15.00
13	XD-1.0-13Y	12.00	16.00
14	XD-1.0-14Y	13.00	17.00
15	XD-1.0-15Y	14.00	18.00
16	XD-1.0-16Y	15.00	19.00

Ordering Information



GENERAL TOLERANCE			制图 DRAWING	02	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品料号 PART NO.	XD-1.0-NY	单位 UNITS	mm
X.XX ±0.20			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
X.XXX ±0.10								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					