



SECTION:A-A



SECTION:B-B



- SPECIFICATIONS
- 1、 Current Rating: 1A AC, DC
  - 2、 Voltage Rating: 50V AC, DC
  - 3、 Temperatuer Range: -25°C~ +85°C
  - 4、 Contact Resistance: 20mΩ Max
  - 5、 Insulation Resistance: 100mΩ Min
  - 6、 Withstanding Voltang: 500V AC/minute
  - 7、 Material: Phosphoric brass Tin-plated
  - 8、 Applicable Wire Sizes:AWG #26~32#

|           |                        |                   |                   |                  |    |   |         |             |     |
|-----------|------------------------|-------------------|-------------------|------------------|----|---|---------|-------------|-----|
|           |                        |                   | GENERAL TOLERANCE | 制图<br>DRAWING    | 02 | 深圳讯答科技有限公司<br>ShenzhenXundaTechnology Co.,Ltd |         |             |     |
|           |                        |                   | DIM TOL           | 审核<br>CHECK      |    |   |         |             |     |
|           |                        |                   | X.X ±0.30         | 批准<br>APPROVAL   |    | 产品料号<br>PART NO.                              | XD-GH-T | 单位<br>UNITS | mm  |
|           |                        |                   | X.XX ±0.20        | 投影<br>Projection |    | 材料<br>MATERIAL                                |         | 页次<br>SHEET | 1/1 |
|           |                        |                   | X.XXX ±0.10       |                  |    |   |         |             |     |
|           |                        |                   | Angle ±3.0°       |                  |    |   |         |             |     |
| 1         | 初版发行                   |                   |                   |                  |    |   |         |             |     |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE |                   |                  |    |   |         |             |     |