


SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperaturer Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltang: 800V AC/minute
7. Material: Housing Nylon66 UL94-VO

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-PHB-2x2Y-X	2.00	7.00	4.70
3	XD-PHB-2x3Y-X	4.00	9.00	6.70
4	XD-PHB-2x4Y-X	6.00	11.00	8.70
5	XD-PHB-2x5Y-X	8.00	13.00	10.70
6	XD-PHB-2x6Y-X	10.00	15.00	12.70
7	XD-PHB-2x7Y-X	12.00	17.00	14.70
8	XD-PHB-2x8Y-X	14.00	19.00	16.70
9	XD-PHB-2x9Y-X	16.00	21.00	18.70
10	XD-PHB-2x10Y-X	18.00	23.00	20.70
11	XD-PHB-2x11Y-X	20.00	25.00	22.70
12	XD-PHB-2x12Y-X	22.00	27.00	24.70
13	XD-PHB-2x13Y-X	24.00	29.00	26.70
14	XD-PHB-2x14Y-X	26.00	31.00	28.70
15	XD-PHB-2x15Y-X	28.00	33.00	30.70
16	XD-PHB-2x16Y-X	30.00	35.00	32.70
17	XD-PHB-2x17Y-X	32.00	37.00	34.70
18	XD-PHB-2x18Y-X	34.00	39.00	36.70
19	XD-PHB-2x19Y-X	36.00	41.00	38.70
20	XD-PHB-2x20Y-X	38.00	43.00	40.70
21	XD-PHB-2x21Y-X	40.00	45.00	42.70
22	XD-PHB-2x22Y-X	42.00	47.00	44.70
30	XD-PHB-2x30Y-X	58.00	63.00	60.70

Ordering Information

XD - PHB - N *** - *



			GENERAL TOLERANCE	制图 DRAWING	05	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-PHB-2xNY-X	单位 UNITS	mm
			X.XX ±0.20	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						