


SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer LCP UL94-VO
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2ALT-XX	2.00	8.00
3	XD-HY-3ALT-XX	4.00	10.00
4	XD-HY-4ALT-XX	6.00	12.00
5	XD-HY-5ALT-XX	8.00	14.00
6	XD-HY-6ALT-XX	10.00	16.00
7	XD-HY-7ALT-XX	12.00	18.00
8	XD-HY-8ALT-XX	14.00	20.00
9	XD-HY-9ALT-XX	16.00	22.00
10	XD-HY-10ALT-XX	18.00	24.00
11	XD-HY-11ALT-XX	20.00	26.00
12	XD-HY-12ALT-XX	22.00	28.00
13	XD-HY-13ALT-XX	24.00	30.00
14	XD-HY-14ALT-XX	26.00	32.00
15	XD-HY-15ALT-XX	28.00	34.00
16	XD-HY-16ALT-XX	30.00	36.00

Ordering Information

XD - HY - N *** - **



			GENERAL TOLERANCE	制图 DRAWING	01	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-HY-NALT-XX	单位 UNITS	mm
			X.XX ±0.20	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°						