


- SPECIFICATIONS**
1. Current Rating: 2A AC, DC
  2. Voltage Rating: 250V AC, DC
  3. Temperature Range: -25°C~ +85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 1000mΩ Min
  6. Withstanding Voltage: 1000V AC/minute
  7. Material: Wafer LCP UL94-VO  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-HY-2AWT-XX	2.00	8.00
3	XD-HY-3AWT-XX	4.00	10.00
4	XD-HY-4AWT-XX	6.00	12.00
5	XD-HY-5AWT-XX	8.00	14.00
6	XD-HY-6AWT-XX	10.00	16.00
7	XD-HY-7AWT-XX	12.00	18.00
8	XD-HY-8AWT-XX	14.00	20.00
9	XD-HY-9AWT-XX	16.00	22.00
10	XD-HY-10AWT-XX	18.00	24.00
11	XD-HY-11AWT-XX	20.00	26.00
12	XD-HY-12AWT-XX	22.00	28.00
13	XD-HY-13AWT-XX	24.00	30.00
14	XD-HY-14AWT-XX	26.00	32.00
15	XD-HY-15AWT-XX	28.00	34.00
16	XD-HY-16AWT-XX	30.00	36.00

**Ordering Information**

XD - HY - N \*\*\* - \*\*



GENERAL TOLERANCE			制图 DRAWING	01	<b>深圳讯答科技有限公司</b> ShenzhenXunDaTechnology Co.,Ltd			
			审核 CHECK		产品名称 TITLE	HY (2.00) 单排带扣 卧贴	版本 REV.	A
			批准 APPROVAL		产品料号 PART NO.	XD-HY-NAWT-XX	单位 UNITS	mm
1	初版发行		比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection				