


SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP UL94-V0  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-HA-2AWT-XX	2.50	10.00	7.50
3	XD-HA-3AWT-XX	5.00	12.50	10.00
4	XD-HA-4AWT-XX	7.50	15.00	12.50
5	XD-HA-5AWT-XX	10.00	17.50	15.00
6	XD-HA-6AWT-XX	12.50	20.00	17.50
7	XD-HA-7AWT-XX	15.00	22.50	20.00
8	XD-HA-8AWT-XX	17.50	25.00	22.50
9	XD-HA-9AWT-XX	20.00	27.50	25.00
10	XD-HA-10AWT-XX	22.50	30.00	27.50
11	XD-HA-11AWT-XX	25.00	32.50	30.00
12	XD-HA-12AWT-XX	27.50	35.00	32.50

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	01	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-HA-NAWT-XX	单位 UNITS	mm
			X.XX ±0.20		比例 SCALE				
			X.XXX ±0.10		投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°			材料 MATERIAL	页次 SHEET		1/1