



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltage: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-VH-2A2W-G	3.96	7.92
3	HC-VH-3A2W-G/ HC-VH-3A3W-G	7.92	11.88
4	HC-VH-4A4W-G	11.88	15.84
5	HC-VH-5A5W-G	15.84	19.80
6	HC-VH-6A6W-G	19.80	23.76
7	HC-VH-7A7W-G	23.76	27.72
8	HC-VH-8A8W-G	27.72	31.68
9	HC-VH-9A9W-G	31.68	35.64
10	HC-VH-10A10W-G	35.64	39.60

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD				
			DIM TOL	审核 CHECK		产品名称 TITLE	VH 高弯	版本 REV.	A
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	HC-VH-NANW-G	单位 UNITS	mm
1	初版发行		X.XX ±0.20	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投影 Projection					
			Angle ±3.0°						