


PCB LAYOUT

SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
4. Contact Resistance: $20\text{m}\Omega$ Max
5. Insulation Resistance: $1000\text{m}\Omega$ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-HY-2AW-X	2.00	6.00
3	HC-HY-3AW-X	4.00	8.00
4	HC-HY-4AW-X	6.00	10.00
5	HC-HY-5AW-X	8.00	12.00
6	HC-HY-6AW-X	10.00	14.00
7	HC-HY-7AW-X	12.00	16.00
8	HC-HY-8AW-X	14.00	18.00
9	HC-HY-9AW-X	16.00	20.00
10	HC-HY-10AW-X	18.00	22.00
11	HC-HY-11AW-X	20.00	24.00
12	HC-HY-12AW-X	22.00	26.00
13	HC-HY-13AW-X	24.00	28.00
14	HC-HY-14AW-X	26.00	30.00
15	HC-HY-15AW-X	28.00	32.00
16	HC-HY-16AW-X	30.00	34.00

Ordering Information



			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK		产品名称 TITLE		版本 REV.	A
			X, X	±0.30	批准 APPROVAL		HY (2.0) 弯针			
			X, XX	±0.20	比例 SCALE		产品料号 PART NO.		单位 UNITS	mm
			X, XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								