



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE ± 0.05)

**SPECIFICATIONS**

Rated Current:3.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:1000V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°c to +105°c

Contact Material:Brass  
Contact Plating:Au Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

**Ordering Information**

PZ 254 - \* - N - Z - \* - \*\*

No. of Rows 1=Single Row 2=Dual Row 3=Third Row	No. of Pins 2-40Pin	Type N=直插 D=贴片 S=注塑 Z=带锁	Length (mm/英寸)	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
--	------------------------	--------------------------------------	-------------------	--

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK		产品名称 TITLE	2.54 三排 直排针	版本 REV.	A
			X.X	±0.30	批准 APPROVAL		产品料号 PART NO.	PZ254-3-N-Z-11.5-XX	单位 UNITS	mm
			X.XX	±0.20	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
			X.XXX	±0.10	投影 Projection					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°						