
ITEM I	NO. PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	54-00241	Connector, 4 pin M12 A-code socket, 12xL21.5mm, gold plated, panel mount, solder cup, IP67	1	nut and o-ring included
2	Wire	Wire, hook-up, TS, 24 AWG, UL 11028, 600V, 105C, 1.1 mm, mPPE	4	color: red, yello, black, white
3	Heat shrink	Heat shrink, UL, black	4	covers solder joints



Notes:

Cable rated for 250 V, 4 A Temperature: -40 ~ 105 °C

IP67 waterproof rating when mated with corresponding (IP67) connector and installed properly in panel

Cables individually packaged in PE bag Functionally equivalent components may be substituted

5



Front View Not to Scale

Wiring Diagram						
54-00241	wire color (P/N)					
1	red (30-01762)					
2	yellow (30-01765)					
3	black (30-01763)					
4	white (30-01764)					

Revision:	Date:	Description:	Prepared:	Notes:					
Α	11/7/2022	Initial release		RoHS compliant		$\Box$	JSII	ITY	
			Verified:	Function test: no open, no short circuit, no intermittent	tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com				
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X XX: + 0.05 mm	millimeters. Tolerances: X· + 0.5 mm Descri	Description: Cable, 305 mm, M12 4C socket panel mount 54-	Size: Part number: A 10-05260			
				00241 to blunt cut, 24 AWG, UL 11028 hook-up wire	Scale:	1:1		Sheet 1 of 1	

3 2