

Universal Reversible USB 2.0 Cable (Reversible A to Left-Angle 5Pin Mini B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR030-006-LAB



Universal / Reversible "A" connector allows plugging in any direction

Features

- Universal / Reversible "A" connector plugs in any direction
- Left-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Specifications

OVERVIEW	
UPC Code	037332182289
Technology	USB 2.0 (High Speed)
Cable Type	Passive
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83

Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Left-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Left-Angle Mini-B Device Cable (A Male to 5Pin Mini-B Male)

Shipping Dimensions (hwd / in.)	0.10 x 7.00 x 10.00
Shipping Dimensions (hwd / cm)	0.25 x 17.78 x 25.40
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB MINI-B 5-PIN (MALE)
Connector Style	Angled
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty