

### **Model 73072**

SMB Jack to SMB Jack, RG316/U (50 Ohm), RG179B/U (75 Ohm)

# Snap-on coupling and small size for fast connect and disconnect

#### **Features**

- Small size and durability for confident connections.
- Connectors are precision machined and gold-plated for low loss.
- Perfect for applications where space, weight, performance and ease of connections are required.

#### **Materials**

SMB Male Connectors (50 Ohm):

Center Contact: Beryllium Copper, Gold Plated

Connector Body: Brass, Gold Plated Crimp Ferrule: Copper, Nickel Plated

Insulators: PTFE


SMB Male Connectors (75 Ohm):

Center Contact: Brass, Gold Plated Connector Body: Brass, Gold Plated Crimp Ferrule: Copper, Nickel Plated

Insulators: Silicone Rubber

### **Specifications**

Cable Type	RG316/U	RG179B/U
Impedance	50Ω	75Ω
Frequency Range	DC - 4GHz	DC - 2GHz
Capacitance per 1ft (0.305m)	29.0 pF	19.5 pF
Insulation Resistance	≥ 1000 MΩ	≥ 10,000 MΩ
Insulator Withstand	750V	750V
Temperature Range	-65°C to +165°C (-85°F to +329°F)	-65°C to +165°C (-85°F to +329°F)
Jacket	FEP	FEP
Cable O.D. (inches)	0.098" (2.5mm))	0.100" (2.54mm)
Center Conductor (mm)	7 x .18 silver coated copper covered steel	7 x .1 silver coated copper covered steel



**USA:** Technical Support: <u>technicalsupport@pomonatest.com</u>

**Europe:** 31-(0) 40 2675 150 International: 425-446-5500


Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.



### **Model 73072**

SMB Jack to SMB Jack, RG316/U (50 Ohm), RG179B/U (75 Ohm)



## **Ordering Information**

Model: 73072

Cable Designators: **BB** = RG316/U, **VV** = RG179B/U Standard Lengths: **6"**, **12"**, **24"**, **36"**, **48"**, **60"** 

- 6" ± .118" (152mm ± 3mm) (73072-BB only)
- 12" ± .157" (305mm ± 4mm) (73072-BB only)
- 24" ± .275" (610mm ± 7mm)
- 36" ± .394" (914mm ± 10mm)
- 48" ± .512" (1219mm ± 13mm)
- 60" ± .630" (1524mm ± 16mm) (73072-VV only)

Ordering Example: 73072-VV-48

Cable is RG179B/U with length of 48" (1219mm)



73072-VV SMB Jack to SMB Jack, RG179B/U, 75 Ohm

**USA:** Technical Support: <u>technicalsupport@pomonatest.com</u>

**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.