



Product: [9430MN](#)

SpaceMaker™, 7 C #22 Str TC, PO Ins, PVC Jkt, AWM 2937



Request Sample

## Product Description

SpaceMaker™, 7 Conductor 22AWG (19x34) Tinned Copper, PO Insulation, PVC Outer Jacket, AWM 2937

## Technical Specifications

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	7	22 AWG	19x34	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.050 in (1.3 mm)	Black, White, Red, Dark Green, Brown, Dark Blue, Orange

#### Outer Shield

Material
No Shield

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.182 in

Overall Cable Diameter (Nominal): 0.182 in.

### Electrical Characteristics

#### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedence	Max. Current
18.1 Ohm/1000ft	16.6 pF/ft (54.5 pF/m)	51 Ohm	2.1 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

#### Bend Radius

Stationary Min.	Installation Min.	Flexing Min.
0.730 in (18.5 mm)	0.730 in	1.820 in (46.23 mm)

Max. Pull Tension: 66 lbs (30 kg)

Bulk Cable Weight: 25 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	FT2
AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
Other Standard Compliance(s):	NFPA 79

## History

Update and Revision:	Revision Number: 0.203 Revision Date: 05-05-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
9430MN 006100	Blue, Light	Reel	100 ft	612825388746
9430MN 0061000	Blue, Light	Reel	1,000 ft	612825388753
9430MN 008100	Gray	Reel	100 ft	612825388760
9430MN 0081000	Gray	Reel	1,000 ft	612825388777
9430MN 004100	Yellow	Reel	100 ft	612825388722
9430MN 0041000	Yellow	Reel	1,000 ft	612825388739

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.