

## FireWire® - 6-ft. Firewire IEEE 1394 Gold 6Pin/4Pin Cable

MODEL NUMBER: F007-006-R



### Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. This 6ft. IEEE-1394 Firewire cable has 6-pin male to 4-pin male connectors, supports data transmission of 100~400Mbps and is used most commonly to connect a PC device to an A/V device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. clamshell retail packaging.

### Features

- All Tripp Lite Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

## Specifications

OVERVIEW	
UPC Code	037332012012
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83

### Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity
- Retail Packaging

### System Requirements

- Firewire 1394 device with a 6-Pin connector and a Firewire device with a 4-Pin connector

### Package Includes

- 6-ft. Firewire (IEEE 1394) Cable  
6 Pin to 4 Pin with Gold Connectors

Shipping Dimensions (hwd / in.)	6.75 x 5.75 x 1.50
Shipping Dimensions (hwd / cm)	17.14 x 14.60 x 3.81
Shipping Weight (lbs.)	0.29
Shipping Weight (kg)	0.13
<b>CONNECTIONS</b>	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	4 PIN (MALE)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty