

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 17-position, shielded, free cable end, on Socket straight M12, coding: A SPEEDCON, cable length: 15 m

Commercial data

Item number	1079460
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Sales key	BF03
Product key	BF1CNA
GTIN	4055626799292
Weight per piece (including packing)	1,633.7 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	DE

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	17
Shielded	yes

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	17
Coding type	A
Number of positions	17
Locking type	SPEEDCON

Cable/line

Cable length	15 m
--------------	------

Black PUR/PVC twisted pair [35T]

Dimensional drawing	
Cable weight	105 kg/km
UL AWM Style	20233 / 1061 (80°C/300 V)
Number of positions	17
Shielded	yes
Cable type	Black PUR/PVC twisted pair [35T]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross section	17x 0.14 mm ² (Signal line)
Wire diameter incl. insulation	1 mm ±0.05 mm (Signal line)
External cable diameter	9.2 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Single wire, color	white-brown, green-yellow, gray-pink, blue-red, black-violet, gray/pink-red/blue, white/green-brown/green, white/yellow-yellow/brown-white/gray
Overall twist	7 pairs and 1 three-way unit, intertwisted
Optical shield covering	85 %
Max. conductor resistance	142 Ω/km (at 20 °C)
Insulation resistance	≥ 10 MΩ*km (at 20 °C)
Nominal voltage, cable	42 V AC
Test voltage	1500 V AC
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Max. bending cycles	4000000
Flame resistance	According to DIN EN 60332-1-2 According to VW-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	hydrolysis and microbe resistant in accordance with EN 50396
Special properties	Flexible cable conduit capable
Ambient temperature (operation)	-30 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1079460>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00385

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-17P-15,0-35T/FS SH SCO - Sensor/actuator cable



1079460

<https://www.phoenixcontact.com/us/products/1079460>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com