

	1	2	3	4	5	6	7																																																																	
A								A																																																																
B								B																																																																
C								C																																																																
D	<p style="text-align: center;">PIN OUT</p> <table border="1"> <tr> <td>CN1</td> <td>WIRE COLOR</td> <td>CN2</td> </tr> <tr> <td>1</td> <td>ORANGE/WHITE</td> <td>1</td> </tr> <tr> <td>2</td> <td>ORANGE</td> <td>2</td> </tr> <tr> <td>3</td> <td>GREEN/WHITE</td> <td>3</td> </tr> <tr> <td>6</td> <td>GREEN</td> <td>6</td> </tr> <tr> <td>4</td> <td>BLUE</td> <td>4</td> </tr> <tr> <td>5</td> <td>BLUE/WHITE</td> <td>5</td> </tr> <tr> <td>7</td> <td>BROWN/WHITE</td> <td>7</td> </tr> <tr> <td>8</td> <td>BROWN</td> <td>8</td> </tr> <tr> <td>SHELL</td> <td>BRAID</td> <td>SHELL</td> </tr> </table> <p>Electrical test: Open/short/intermittence: 100%</p> <table border="1"> <tr> <td>③</td> <td>Molding</td> <td>PVC 45P Color: see order code</td> <td>NA</td> <td>KG</td> </tr> <tr> <td>②</td> <td>CONNECTOR</td> <td>RJ45 8P8C two fork 3u" gold plated with metal shield</td> <td>2</td> <td>PCS</td> </tr> <tr> <td>①</td> <td>CABLE</td> <td>CAT5e S/FTP (26AWG+1PR)4+A+B+PVC OD=5.4±0.3MM Color: see order code</td> <td>NA</td> <td>MM</td> </tr> <tr> <td>NO:</td> <td>NAME</td> <td>DESCRIPTION</td> <td>QTY</td> <td>UNIT</td> </tr> </table> <p>WSW order code AMJF0808-xxxx-xxB</p> <p>Cable length</p> <ul style="list-style-type: none"> 0030: 0.3M 0050: 0.5M 0100: 1.0M 0150: 1.5M 0200: 2.0M 0300: 3.0M 0500: 5.0M 0700: 7.0M 1000: 10M 1500: 15M <p>Cable&Molding color</p> <ul style="list-style-type: none"> BK: Black RD: Red YE: Yellow GN: Green GY: Grey BU: Blue WH: White BN: Brown 							CN1	WIRE COLOR	CN2	1	ORANGE/WHITE	1	2	ORANGE	2	3	GREEN/WHITE	3	6	GREEN	6	4	BLUE	4	5	BLUE/WHITE	5	7	BROWN/WHITE	7	8	BROWN	8	SHELL	BRAID	SHELL	③	Molding	PVC 45P Color: see order code	NA	KG	②	CONNECTOR	RJ45 8P8C two fork 3u" gold plated with metal shield	2	PCS	①	CABLE	CAT5e S/FTP (26AWG+1PR)4+A+B+PVC OD=5.4±0.3MM Color: see order code	NA	MM	NO:	NAME	DESCRIPTION	QTY	UNIT	D														
CN1	WIRE COLOR	CN2																																																																						
1	ORANGE/WHITE	1																																																																						
2	ORANGE	2																																																																						
3	GREEN/WHITE	3																																																																						
6	GREEN	6																																																																						
4	BLUE	4																																																																						
5	BLUE/WHITE	5																																																																						
7	BROWN/WHITE	7																																																																						
8	BROWN	8																																																																						
SHELL	BRAID	SHELL																																																																						
③	Molding	PVC 45P Color: see order code	NA	KG																																																																				
②	CONNECTOR	RJ45 8P8C two fork 3u" gold plated with metal shield	2	PCS																																																																				
①	CABLE	CAT5e S/FTP (26AWG+1PR)4+A+B+PVC OD=5.4±0.3MM Color: see order code	NA	MM																																																																				
NO:	NAME	DESCRIPTION	QTY	UNIT																																																																				
E	<p style="text-align: center;">RoHS compliant</p> <p style="text-align: center;">Unit: mm</p>							E																																																																
F	<table border="1"> <tr> <td>Scale</td> <td>Free</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td colspan="2">TOLERANCE</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td colspan="2">DIM</td> <td>TOL</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td colspan="2">Angle</td> <td>TOL</td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>Id.</td> <td>Drawn</td> <td>Modification</td> <td>Date</td> <td>Name</td> <td>Date</td> <td>Name</td> <td>Customer-No.</td> </tr> <tr> <td>①</td> <td>Drawn</td> <td></td> <td>30.03.2017</td> <td>Amy</td> <td>30.03.2017</td> <td>Amy</td> <td>ASSMANN WSW-No. AMJF0808-xxxx-xxB</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>Drawing-No. ASS 7946 CA</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>Replace Sheet</td> </tr> </table>							Scale	Free							TOLERANCE								DIM		TOL						Angle		TOL						Id.	Drawn	Modification	Date	Name	Date	Name	Customer-No.	①	Drawn		30.03.2017	Amy	30.03.2017	Amy	ASSMANN WSW-No. AMJF0808-xxxx-xxB								Drawing-No. ASS 7946 CA								Replace Sheet	F
Scale	Free																																																																							
TOLERANCE																																																																								
DIM		TOL																																																																						
Angle		TOL																																																																						
Id.	Drawn	Modification	Date	Name	Date	Name	Customer-No.																																																																	
①	Drawn		30.03.2017	Amy	30.03.2017	Amy	ASSMANN WSW-No. AMJF0808-xxxx-xxB																																																																	
							Drawing-No. ASS 7946 CA																																																																	
							Replace Sheet																																																																	
G	<p style="text-align: center;">ASSMANN</p> <p style="text-align: center;">WSW components</p>							G																																																																
H	<p style="text-align: center;">1 2 3 4 5 6 7</p>							H																																																																