

Mini DisplayPort 1.2 to DVI Adapter Cable (M/M), 1080p, 6 ft. (1.8 m)

MODEL NUMBER: P586-006-DVI



Connect a Computer with Mini Displayport to a DVI enabled Monitor

Description

The P586-006-DVI Mini-DisplayPort to DVI cable allows you to connect a computer with Mini-DisplayPort video output to a DVI-enabled Mmonitor. It features a low-profile DVI connector that fits neatly into the available monitor space without jamming between the wall and the back of the display or impeding neighboring connectors. Male to Male design eliminates the need for separate adapter and cable. In-line passive adapter is designed for use with Dual Mode (DP++) DisplayPort graphics cards. Supports 1920 x 1200 resolution, as well as HDTV 1080p .

Features

- 6-ft. (1.83 m) Mini Displayport to DVI Adapter cable
- Supports 1080P video, as well as audio (if video card enabled)
- Low-profile DVI connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- In-line Passive adapter
- Plug-and-Play
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

Specifications

OVERVIEW	
UPC Code	037332180766
Product Type	Passive Cable
Technology	DVI; DisplayPort
Cable Type	Passive

Highlights

- All in one Mini Displayport to DVI cable design
- Supports 1080P 1920x1080 resolution
- Low-profile DVI connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Computer with Mini Displayport video port
- DVI Monitor
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P586-006-DVI-V2

Package Includes

- 6-ft. (1.83 m) Mini Displayport to DVI Adapter Cable

VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
Max Supported Color Depth	24-bit True Color
HDR Support	No
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.0 +/- 15mm
Wire Gauge (AWG)	32
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% to 85%, Non-Condensing
Operating Humidity Range	0% to 85%, Non-Condensing
Storage Humidity Range	0% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Latching or Gripping Connector	No

FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty