

TOLERANCE TABLE	
TH IN INCHES/FT [METERS]	TOLERANCE
90″ [0 - 0.607]	±0.25″ [0.006]
59.00″ [0.610 - 1.499]	±0.50″ [0.013]
4.9' [1.524 - 7.617]	±2.5%
UP [7.620 & UP]	±5.0%