

Important Note

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks.

MTP/MPO Fan-Out Cable, MTP/MPO to 4xLC, 40GbE, 40GBASE-SR4, OM3 Plenum-Rated - Aqua, 2M (6 ft.)

MODEL NUMBER: N844-02M-8LC-P



Features

- MTP / MPO to 8 x LC, 2 Meter Fan-out Cable
- 40GbE rated OM3 50/125 Multimode
- Plenum rated jacket

Specifications

OVERVIEW		
UPC Code	037332173768	
Technology	Multimode	
Optical Mode	ОМЗ	
PHYSICAL		
Cable Jacket Color	Aqua	
Connector Color	Aqua; Black; Gray	
Cable Jacket Material	PVC	
Cable Jacket Rating	OFNP	
Clad Diameter (microns)	125	

Highlights

- MTP / MPO to 8 x LC Fan-out Cable
- OM3, 40GbE rated, 40GBASE-SR4
- 50/125 Multimode

Package Includes

 2M (6-ft.) MTP / MPO Fan-out Cable, MTP/MPO to 8 x LC, 40GbE OM3 Plenum



Core Diameter (microns)	50	
Number of Fibers	8	
Cable Length (ft.)	6.6	
Cable Length (m)	2.01	
Cable Length (in.)	78.7	
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)	
Shipping Dimensions (hwd / in.)	0.25 x 4.90 x 6.00	
Shipping Dimensions (hwd / cm)	0.64 x 12.45 x 15.24	
Shipping Weight (lbs.)	0.10	
Shipping Weight (kg)	0.05	
Fiber Cable Length	2M (6.6 ft)	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	5% to 85% RH, Non-Condensing	
Storage Humidity Range	35% to 65% RH, Non-Condensing	
COMMUNICATIONS		
Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps	
Attenuation @ 850NM	3.0 dB/km	
Insertion Loss	0.35 dB	
CONNECTIONS		
Side A - Connector 1	12-STRAND MTP/MPO (FEMALE)	
Side B - Connector 1	(8) LC DUPLEX (MALE)	
Endface Polish	PC	
FEATURES & SPECIFICATIONS		
Push/Pull Tabs	No	
Breakout	Yes	
Trunk	Yes	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		



Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.