



NOTE: ALL MATERIAL COMPLIANT ROHS STANDARD



INK MARKING <FP2053> : YFC CAT.7 SSTP PATCH 3P VERIFIED TO ANSI/TIA-568.2-D & ISO/IEC 11801 ED.2 & EN 50288-4-2 & IEC 60332-1-2 ▲ 26AWGX4P CMX(UL)



Jacket Color
BU608
GY177

orange 1	green 2
white/orange	white/green
blue 3	brown 4
white/blue	white/brown

PINOUT		
P1	WIRE	P2
1	WHITE/ORANGE	1
2	ORANGE	2
3	WHITE/GREEN	3
6	GREEN	6
5	WHITE/BLUE	5
4	BLUE	4
7	WHITE/BROWN	7
8	BROWN	8
SHELL	BRAID	SHELL

Operation Temperature:-20°C~+60°C  
 conductor resistance: $152 \downarrow (\Omega/\text{Km})$  at 20°C

L(ft)	T(inch)	T(%)	L(ft)	T(inch)	T(%)
1	$\pm 1.2$	10%	15	$\pm 3.15$	1.75%
2	$\pm 1.2$	5%	20	$\pm 4$	1.67%
3	$\pm 1.2$	3.33%	25	$\pm 4$	1.33%
4	$\pm 1.2$	2.5%	30	$\pm 6$	1.67%
5	$\pm 1.2$	2%	40	$\pm 6$	1.25%
6	$\pm 1.2$	1.67%	50	$\pm 6$	1.0%
7	$\pm 2$	2.38%	60	$\pm 6$	1.0%
8	$\pm 2$	2.08%	70	$\pm 6$	0.67%
9	$\pm 2$	1.85%	80	$\pm 6$	0.59%
10	$\pm 2$	1.67%	90	$\pm 6$	0.5%
12	$\pm 2$	1.39%	100	$\pm 6$	0.5%



③	MOLD	PVC YUS-07	A/R	Kg
②	PLUG	8P8C 50U RJ45	2	PCS
①	CABLE	CAT.7 SSTP PVC 26AWG*4P TC	A/R	M
NO.	PART NAME	SPECIFICATION DESCRIPTION	QT'Y	UNIT


Drawn By:	Date: 10 / 28 / 2022	Description: Cat.7 Shielded Cables
Checked By:	Sheet 1 of 2	Model No. CM-1003XXXXBSTK
Approved By:	Scale 1:1	Rev. 01 Unit: mm

NOTE: CARTON MATERIAL MUST BE A=A

**Cable Part No. Color Guide** \*Replace "XX" in the Part No. to the respective color code (e.x. CM-100322GNBSTK for a Green cable)



White = WT  
  Gray = GY  
  Black = BK  
  Blue = BL  
  Green = GN  
  Purple = PU  
  Yellow = YW  
  Orange = OR  
  Red = RD

Front



PE BAG SIZE(INCH)	PART NO.	length/FT	CARION SIZE(INCH)	Q'TY	G.W(LBS)
6.89x7.48	CM-100322XXBSTK	3	15.75x15.75x7.87	150	18.7
7.87x9.45	CM-100329XXBSTK	7	15.75x15.75x9.06	80	25.52
6.89x9.06	CM-100326XXBSTK	7	15.75x15.75x7.87	100	23.54
7.87x9.45	CM-100332XXBSTK	20	16.54x16.54x10.24	60	35.42
9.25x10.63	CM-100333XXBSTK	25	15.75x15.75x7.87	35	25.52
9.25x11.81	CM-100336XXBSTK	50	15.75x15.75x7.87	20	28.16
9.25x11.81	CM-100338XXBSTK	70	15.75x15.75x9.06	20	38.5
9.25x11.81	CM-100339XXBSTK	80	15.75x15.75x9.06	20	42.9
9.25x14.96	CM-100340XXBSTK	90	16.54x16.54x10.24	20	49.28
9.25x14.96	CM-100341XXBSTK	100	16.54x16.54x10.24	20	54.34
6.89x7.48	CM-100324XXBSTK	100	15.75x15.75x7.87	110	19.8

Back



**CABLEMAX**

Drawn By:	Date: 10 / 28 / 2022	Description: Cat.7 Shielded Cables
Checked By:	Sheet 2 of 2	Model No. CM-1003XXXXBSTK
Approved By:	Scale 1:1	Rev. 01    Unit: mm