

Specification Sheet

Part Number: 126-00117



Wing design helps stabilize the tie in high-vibration applications. Includes a ladder-type strap as opposed to a conventional serrated strap which provides the benefit of being extra flexible.

Tie is releasable and reusable giving additional use options.

1-Pc Cable Tie/Arrowhead Mount w/Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66, Natural, 500/bg

Article Number 126-00117

Type T50RSFM

Color Natural (NA)

Quantity Per bag

Product Description
Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description
1-Pc Cable Tie/Arrowhead Mount w/Wings, 8"L, 50lb, 0.24 - 0.26" Hole Dia, PA66, Natural, 500/bg

Global Part Name T50RSFM-PA66-NA

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225.0

Length L (Imperial) 8.0

Length L (Metric) 203.2

Fixation Method Arrowhead

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 1.77

Bundle Diameter Max (Metric) 45.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	.22
Height H (Metric)	5.60
Panel Thickness Min (Imperial)	0.028
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.24 -0.26
Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.6

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)